

頁	商品名	修正内容	修正後																																																																																		
262	プリカチューブ 防水プリカ用附属品 ノックアウト用 防水コネクタ WBG	<p>追加</p> <p>注 1.</p> <table border="1"> <tr> <td>○ WBG 76</td> <td>63</td> <td>76</td> <td>63</td> <td>107.6</td> <td>101.9</td> <td>64.0</td> <td>17</td> </tr> <tr> <td>○ WBG 83</td> <td>83</td> <td>75</td> <td>114.2</td> <td>108.3</td> <td>76.3</td> <td>4</td> </tr> <tr> <td>○ WBG 101-92</td> <td>101</td> <td>87</td> <td>135.9</td> <td>129.6</td> <td>88.2</td> <td>22</td> </tr> <tr> <td>○ WBG 101-104</td> <td>101</td> <td>99</td> <td>135.9</td> <td>135.0</td> <td>100.3</td> <td>22</td> </tr> </table> <p>※印の品番は、JIS C 8350に該当しない製品です。</p> <p>追加</p> <p>注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ WBG 76	63	76	63	107.6	101.9	64.0	17	○ WBG 83	83	75	114.2	108.3	76.3	4	○ WBG 101-92	101	87	135.9	129.6	88.2	22	○ WBG 101-104	101	99	135.9	135.0	100.3	22	<table border="1"> <tr> <td>○ WBG 76</td> <td>63</td> <td>76</td> <td>63</td> <td>107.6</td> <td>101.9</td> <td>64.0</td> <td>17</td> </tr> <tr> <td>○ WBG 83</td> <td>83</td> <td>75</td> <td>114.2</td> <td>108.3</td> <td>76.3</td> <td>4</td> </tr> <tr> <td>○ WBG 101-92</td> <td>101</td> <td>87</td> <td>135.9</td> <td>129.6</td> <td>88.2</td> <td>22</td> </tr> <tr> <td>○ WBG 101-104</td> <td>101</td> <td>99</td> <td>135.9</td> <td>135.0</td> <td>100.3</td> <td>22</td> </tr> </table> <p>注 1. ※印の品番は、JIS C 8350に該当しない製品です。 注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ WBG 76	63	76	63	107.6	101.9	64.0	17	○ WBG 83	83	75	114.2	108.3	76.3	4	○ WBG 101-92	101	87	135.9	129.6	88.2	22	○ WBG 101-104	101	99	135.9	135.0	100.3	22																								
		○ WBG 76	63	76	63	107.6	101.9	64.0	17																																																																												
○ WBG 83	83	75	114.2	108.3	76.3	4																																																																															
○ WBG 101-92	101	87	135.9	129.6	88.2	22																																																																															
○ WBG 101-104	101	99	135.9	135.0	100.3	22																																																																															
○ WBG 76	63	76	63	107.6	101.9	64.0	17																																																																														
○ WBG 83	83	75	114.2	108.3	76.3	4																																																																															
○ WBG 101-92	101	87	135.9	129.6	88.2	22																																																																															
○ WBG 101-104	101	99	135.9	135.0	100.3	22																																																																															
263	プリカチューブ 防水プリカ用附属品 ノックアウト用 防水コネクタ WBC	<table border="1"> <tr> <td>○ WBC 30</td> <td>PEC</td> <td>30</td> <td>23</td> <td>53.8</td> <td>49.5</td> <td>24.6</td> <td>7</td> </tr> <tr> <td>○ WBC 38</td> <td>38</td> <td>30</td> <td>63.6</td> <td>59.3</td> <td>30.8</td> <td>8</td> </tr> <tr> <td>○ WBC 50</td> <td>50</td> <td>42</td> <td>78.6</td> <td>73.8</td> <td>42.9</td> <td>7</td> </tr> <tr> <td>○ WBC 63</td> <td>63</td> <td>53</td> <td>92.4</td> <td>87.2</td> <td>54.7</td> <td>11</td> </tr> <tr> <td>○ WBC 76</td> <td>76</td> <td>63</td> <td>107.6</td> <td>101.9</td> <td>64.0</td> <td>17</td> </tr> </table> <p>追加</p> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ WBC 30	PEC	30	23	53.8	49.5	24.6	7	○ WBC 38	38	30	63.6	59.3	30.8	8	○ WBC 50	50	42	78.6	73.8	42.9	7	○ WBC 63	63	53	92.4	87.2	54.7	11	○ WBC 76	76	63	107.6	101.9	64.0	17	<table border="1"> <tr> <td>○ WBC 30</td> <td>PEC</td> <td>30</td> <td>23</td> <td>53.8</td> <td>49.5</td> <td>24.6</td> <td>7</td> </tr> <tr> <td>○ WBC 38</td> <td>38</td> <td>30</td> <td>63.6</td> <td>59.3</td> <td>30.8</td> <td>8</td> </tr> <tr> <td>○ WBC 50</td> <td>50</td> <td>42</td> <td>78.6</td> <td>73.8</td> <td>42.9</td> <td>7</td> </tr> <tr> <td>○ WBC 63</td> <td>63</td> <td>53</td> <td>92.4</td> <td>87.2</td> <td>54.7</td> <td>11</td> </tr> <tr> <td>○ WBC 76</td> <td>76</td> <td>63</td> <td>107.6</td> <td>101.9</td> <td>64.0</td> <td>17</td> </tr> </table> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ WBC 30	PEC	30	23	53.8	49.5	24.6	7	○ WBC 38	38	30	63.6	59.3	30.8	8	○ WBC 50	50	42	78.6	73.8	42.9	7	○ WBC 63	63	53	92.4	87.2	54.7	11	○ WBC 76	76	63	107.6	101.9	64.0	17										
		○ WBC 30	PEC	30	23	53.8	49.5	24.6	7																																																																												
○ WBC 38	38	30	63.6	59.3	30.8	8																																																																															
○ WBC 50	50	42	78.6	73.8	42.9	7																																																																															
○ WBC 63	63	53	92.4	87.2	54.7	11																																																																															
○ WBC 76	76	63	107.6	101.9	64.0	17																																																																															
○ WBC 30	PEC	30	23	53.8	49.5	24.6	7																																																																														
○ WBC 38	38	30	63.6	59.3	30.8	8																																																																															
○ WBC 50	50	42	78.6	73.8	42.9	7																																																																															
○ WBC 63	63	53	92.4	87.2	54.7	11																																																																															
○ WBC 76	76	63	107.6	101.9	64.0	17																																																																															
263	プリカチューブ 防水プリカ用附属品 ノックアウト用 防水コネクタ W90BG	<p>修正</p> <p>注 1.</p> <table border="1"> <tr> <td>○ W90BG 50-54</td> <td>50</td> <td>48</td> <td>78.6</td> <td>74.0</td> <td>49.8</td> <td>48.0</td> <td>8</td> </tr> <tr> <td>○ W90BG 63</td> <td>63</td> <td>49</td> <td>92.4</td> <td>74.0</td> <td>49.8</td> <td>48.0</td> <td>8</td> </tr> <tr> <td>○ W90BG 63-70</td> <td>63</td> <td>61</td> <td>92.4</td> <td>93.0</td> <td>64.3</td> <td>58.0</td> <td>8</td> </tr> <tr> <td>○ W90BG 76-82</td> <td>76</td> <td>75</td> <td>107.6</td> <td>106.0</td> <td>76.6</td> <td>68.0</td> <td>9</td> </tr> </table> <p>注 1. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部で、最大外径の40～60%の外径を目安として下さい。</p> <p>追加</p> <p>注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ W90BG 50-54	50	48	78.6	74.0	49.8	48.0	8	○ W90BG 63	63	49	92.4	74.0	49.8	48.0	8	○ W90BG 63-70	63	61	92.4	93.0	64.3	58.0	8	○ W90BG 76-82	76	75	107.6	106.0	76.6	68.0	9	<table border="1"> <tr> <td>○ W90BG 50-54</td> <td>50</td> <td>48</td> <td>78.6</td> <td>74.0</td> <td>49.8</td> <td>48.0</td> <td>8</td> </tr> <tr> <td>○ W90BG 63</td> <td>63</td> <td>49</td> <td>92.4</td> <td>74.0</td> <td>49.8</td> <td>48.0</td> <td>8</td> </tr> <tr> <td>○ W90BG 63-70</td> <td>63</td> <td>61</td> <td>92.4</td> <td>93.0</td> <td>64.3</td> <td>58.0</td> <td>8</td> </tr> <tr> <td>○ W90BG 76-82</td> <td>76</td> <td>75</td> <td>107.6</td> <td>106.0</td> <td>76.6</td> <td>68.0</td> <td>9</td> </tr> </table> <p>注 1. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部で、最大外径の40～60%の外径を目安として下さい。 注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ W90BG 50-54	50	48	78.6	74.0	49.8	48.0	8	○ W90BG 63	63	49	92.4	74.0	49.8	48.0	8	○ W90BG 63-70	63	61	92.4	93.0	64.3	58.0	8	○ W90BG 76-82	76	75	107.6	106.0	76.6	68.0	9																		
		○ W90BG 50-54	50	48	78.6	74.0	49.8	48.0	8																																																																												
○ W90BG 63	63	49	92.4	74.0	49.8	48.0	8																																																																														
○ W90BG 63-70	63	61	92.4	93.0	64.3	58.0	8																																																																														
○ W90BG 76-82	76	75	107.6	106.0	76.6	68.0	9																																																																														
○ W90BG 50-54	50	48	78.6	74.0	49.8	48.0	8																																																																														
○ W90BG 63	63	49	92.4	74.0	49.8	48.0	8																																																																														
○ W90BG 63-70	63	61	92.4	93.0	64.3	58.0	8																																																																														
○ W90BG 76-82	76	75	107.6	106.0	76.6	68.0	9																																																																														
263	プリカチューブ 防水プリカ用附属品 ノックアウト用 防水コネクタ W90BC	<p>修正</p> <p>注 1.</p> <table border="1"> <tr> <td>○ W90BC 24</td> <td>PEC</td> <td>24</td> <td>18</td> <td>47.2</td> <td>35.5</td> <td>19.4</td> <td>24.5</td> <td>5</td> </tr> <tr> <td>○ W90BC 30</td> <td>30</td> <td>23</td> <td>53.8</td> <td>42.5</td> <td>24.6</td> <td>28.5</td> <td>5</td> </tr> <tr> <td>○ W90BC 38</td> <td>38</td> <td>30</td> <td>63.6</td> <td>50.0</td> <td>31.0</td> <td>32.6</td> <td>6</td> </tr> <tr> <td>○ W90BC 50</td> <td>50</td> <td>37</td> <td>78.6</td> <td>65.0</td> <td>38.4</td> <td>40.6</td> <td>7</td> </tr> <tr> <td>○ W90BC 63</td> <td>63</td> <td>49</td> <td>92.4</td> <td>79.0</td> <td>49.8</td> <td>48.0</td> <td>8</td> </tr> </table> <p>注 1. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部で、最大外径の40～60%の外径を目安として下さい。</p> <p>追加</p> <p>注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ W90BC 24	PEC	24	18	47.2	35.5	19.4	24.5	5	○ W90BC 30	30	23	53.8	42.5	24.6	28.5	5	○ W90BC 38	38	30	63.6	50.0	31.0	32.6	6	○ W90BC 50	50	37	78.6	65.0	38.4	40.6	7	○ W90BC 63	63	49	92.4	79.0	49.8	48.0	8	<table border="1"> <tr> <td>○ W90BC 24</td> <td>PEC</td> <td>24</td> <td>18</td> <td>47.2</td> <td>35.5</td> <td>19.4</td> <td>24.5</td> <td>5</td> </tr> <tr> <td>○ W90BC 30</td> <td>30</td> <td>23</td> <td>53.8</td> <td>42.5</td> <td>24.6</td> <td>28.5</td> <td>5</td> </tr> <tr> <td>○ W90BC 38</td> <td>38</td> <td>30</td> <td>63.6</td> <td>50.0</td> <td>31.0</td> <td>32.6</td> <td>6</td> </tr> <tr> <td>○ W90BC 50</td> <td>50</td> <td>37</td> <td>78.6</td> <td>65.0</td> <td>38.4</td> <td>40.6</td> <td>7</td> </tr> <tr> <td>○ W90BC 63</td> <td>63</td> <td>49</td> <td>92.4</td> <td>79.0</td> <td>49.8</td> <td>48.0</td> <td>8</td> </tr> </table> <p>注 1. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部で、最大外径の40～60%の外径を目安として下さい。 注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ W90BC 24	PEC	24	18	47.2	35.5	19.4	24.5	5	○ W90BC 30	30	23	53.8	42.5	24.6	28.5	5	○ W90BC 38	38	30	63.6	50.0	31.0	32.6	6	○ W90BC 50	50	37	78.6	65.0	38.4	40.6	7	○ W90BC 63	63	49	92.4	79.0	49.8	48.0	8
		○ W90BC 24	PEC	24	18	47.2	35.5	19.4	24.5	5																																																																											
○ W90BC 30	30	23	53.8	42.5	24.6	28.5	5																																																																														
○ W90BC 38	38	30	63.6	50.0	31.0	32.6	6																																																																														
○ W90BC 50	50	37	78.6	65.0	38.4	40.6	7																																																																														
○ W90BC 63	63	49	92.4	79.0	49.8	48.0	8																																																																														
○ W90BC 24	PEC	24	18	47.2	35.5	19.4	24.5	5																																																																													
○ W90BC 30	30	23	53.8	42.5	24.6	28.5	5																																																																														
○ W90BC 38	38	30	63.6	50.0	31.0	32.6	6																																																																														
○ W90BC 50	50	37	78.6	65.0	38.4	40.6	7																																																																														
○ W90BC 63	63	49	92.4	79.0	49.8	48.0	8																																																																														
265	プリカチューブ 防水プリカ用附属品 電気機器接続用 防水コネクタ W90OG	<p>修正</p> <p>注 1.</p> <table border="1"> <tr> <td>○ W90OG 15</td> <td>PEC</td> <td>15</td> <td>12</td> <td>35.3</td> <td>30.0</td> <td>12.8</td> <td>24</td> <td>43</td> <td>8</td> </tr> <tr> <td>○ W90OG 17</td> <td>17</td> <td>12</td> <td>38.0</td> <td>30.0</td> <td>12.8</td> <td>24</td> <td>44</td> <td>8</td> </tr> <tr> <td>○ W90OG 24</td> <td>24</td> <td>18</td> <td>47.2</td> <td>37.0</td> <td>19.4</td> <td>30</td> <td>50</td> <td>8</td> </tr> </table> <p>注 1. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部でない場合もありますので、最大外径の40～60%の外径を目安として下さい。</p> <p>追加</p> <p>注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ W90OG 15	PEC	15	12	35.3	30.0	12.8	24	43	8	○ W90OG 17	17	12	38.0	30.0	12.8	24	44	8	○ W90OG 24	24	18	47.2	37.0	19.4	30	50	8	<table border="1"> <tr> <td>○ W90OG 15</td> <td>PEC</td> <td>15</td> <td>12</td> <td>35.3</td> <td>30.0</td> <td>12.8</td> <td>24</td> <td>43</td> <td>8</td> </tr> <tr> <td>○ W90OG 17</td> <td>17</td> <td>12</td> <td>38.0</td> <td>30.0</td> <td>12.8</td> <td>24</td> <td>44</td> <td>8</td> </tr> <tr> <td>○ W90OG 24</td> <td>24</td> <td>18</td> <td>47.2</td> <td>37.0</td> <td>19.4</td> <td>30</td> <td>50</td> <td>8</td> </tr> </table> <p>注 1. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部でない場合もありますので、最大外径の40～60%の外径を目安として下さい。 注 2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○ W90OG 15	PEC	15	12	35.3	30.0	12.8	24	43	8	○ W90OG 17	17	12	38.0	30.0	12.8	24	44	8	○ W90OG 24	24	18	47.2	37.0	19.4	30	50	8																										
		○ W90OG 15	PEC	15	12	35.3	30.0	12.8	24	43	8																																																																										
○ W90OG 17	17	12	38.0	30.0	12.8	24	44	8																																																																													
○ W90OG 24	24	18	47.2	37.0	19.4	30	50	8																																																																													
○ W90OG 15	PEC	15	12	35.3	30.0	12.8	24	43	8																																																																												
○ W90OG 17	17	12	38.0	30.0	12.8	24	44	8																																																																													
○ W90OG 24	24	18	47.2	37.0	19.4	30	50	8																																																																													

頁	商品名	修正内容	修正後																																																																																															
266	フリカチューブ 防水プリカ用附属品 防水カップリング WC	<table border="1"> <tr><td>◎</td><td>WC 63</td><td>PEC</td><td>63</td><td>61</td><td>92.4</td><td>63.3</td><td>85</td><td>761</td><td>2</td></tr> <tr><td>◎</td><td>WC 76</td><td></td><td>76</td><td>75</td><td>107.6</td><td>77.2</td><td>78</td><td>936</td><td>2</td></tr> <tr><td>◎</td><td>WC 83</td><td></td><td>83</td><td>80</td><td>114.2</td><td>82.1</td><td>85</td><td>1117</td><td>2</td></tr> <tr><td>◎</td><td>WC 101</td><td></td><td>101</td><td>99</td><td>135.9</td><td>100.8</td><td>89</td><td>1507</td><td>2</td></tr> </table> <p>追加</p> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WC 63	PEC	63	61	92.4	63.3	85	761	2	◎	WC 76		76	75	107.6	77.2	78	936	2	◎	WC 83		83	80	114.2	82.1	85	1117	2	◎	WC 101		101	99	135.9	100.8	89	1507	2	<table border="1"> <tr><td>◎</td><td>WC 63</td><td>PEC</td><td>63</td><td>61</td><td>92.4</td><td>63.3</td><td>85</td><td>761</td><td>2</td></tr> <tr><td>◎</td><td>WC 76</td><td></td><td>76</td><td>75</td><td>107.6</td><td>77.2</td><td>78</td><td>936</td><td>2</td></tr> <tr><td>◎</td><td>WC 83</td><td></td><td>83</td><td>80</td><td>114.2</td><td>82.1</td><td>85</td><td>1117</td><td>2</td></tr> <tr><td>◎</td><td>WC 101</td><td></td><td>101</td><td>99</td><td>135.9</td><td>100.8</td><td>89</td><td>1507</td><td>2</td></tr> </table> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WC 63	PEC	63	61	92.4	63.3	85	761	2	◎	WC 76		76	75	107.6	77.2	78	936	2	◎	WC 83		83	80	114.2	82.1	85	1117	2	◎	WC 101		101	99	135.9	100.8	89	1507	2															
	◎	WC 63	PEC	63	61	92.4	63.3	85	761	2																																																																																								
	◎	WC 76		76	75	107.6	77.2	78	936	2																																																																																								
	◎	WC 83		83	80	114.2	82.1	85	1117	2																																																																																								
◎	WC 101		101	99	135.9	100.8	89	1507	2																																																																																									
◎	WC 63	PEC	63	61	92.4	63.3	85	761	2																																																																																									
◎	WC 76		76	75	107.6	77.2	78	936	2																																																																																									
◎	WC 83		83	80	114.2	82.1	85	1117	2																																																																																									
◎	WC 101		101	99	135.9	100.8	89	1507	2																																																																																									
フリカチューブ 防水プリカ用附属品 水抜き式カップリング WDC	<table border="1"> <tr><td>◎</td><td>WDC 63</td><td>PEC</td><td>63</td><td>61</td><td>92.4</td><td>63.3</td><td>85</td><td>759</td><td>2</td></tr> <tr><td>◎</td><td>WDC 76</td><td></td><td>76</td><td>75</td><td>107.6</td><td>77.2</td><td>78</td><td>930</td><td>2</td></tr> <tr><td>◎</td><td>WDC 83</td><td></td><td>83</td><td>80</td><td>114.2</td><td>82.1</td><td>85</td><td>1114</td><td>2</td></tr> <tr><td>◎</td><td>WDC 101</td><td></td><td>101</td><td>99</td><td>135.9</td><td>100.8</td><td>89</td><td>1494</td><td>2</td></tr> </table> <p>追加</p> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WDC 63	PEC	63	61	92.4	63.3	85	759	2	◎	WDC 76		76	75	107.6	77.2	78	930	2	◎	WDC 83		83	80	114.2	82.1	85	1114	2	◎	WDC 101		101	99	135.9	100.8	89	1494	2	<table border="1"> <tr><td>◎</td><td>WDC 63</td><td>PEC</td><td>63</td><td>61</td><td>92.4</td><td>63.3</td><td>85</td><td>759</td><td>2</td></tr> <tr><td>◎</td><td>WDC 76</td><td></td><td>76</td><td>75</td><td>107.6</td><td>77.2</td><td>78</td><td>930</td><td>2</td></tr> <tr><td>◎</td><td>WDC 83</td><td></td><td>83</td><td>80</td><td>114.2</td><td>82.1</td><td>85</td><td>1114</td><td>2</td></tr> <tr><td>◎</td><td>WDC 101</td><td></td><td>101</td><td>99</td><td>135.9</td><td>100.8</td><td>89</td><td>1494</td><td>2</td></tr> </table> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WDC 63	PEC	63	61	92.4	63.3	85	759	2	◎	WDC 76		76	75	107.6	77.2	78	930	2	◎	WDC 83		83	80	114.2	82.1	85	1114	2	◎	WDC 101		101	99	135.9	100.8	89	1494	2																
◎	WDC 63	PEC	63	61	92.4	63.3	85	759	2																																																																																									
◎	WDC 76		76	75	107.6	77.2	78	930	2																																																																																									
◎	WDC 83		83	80	114.2	82.1	85	1114	2																																																																																									
◎	WDC 101		101	99	135.9	100.8	89	1494	2																																																																																									
◎	WDC 63	PEC	63	61	92.4	63.3	85	759	2																																																																																									
◎	WDC 76		76	75	107.6	77.2	78	930	2																																																																																									
◎	WDC 83		83	80	114.2	82.1	85	1114	2																																																																																									
◎	WDC 101		101	99	135.9	100.8	89	1494	2																																																																																									
フリカチューブ 防水プリカ用附属品 防水コンビネーション カップリング WUG	<table border="1"> <tr><td>◎</td><td>WUG 76</td><td>76</td><td>G70</td><td>CTG70</td><td>69</td><td>107.6</td><td>70.1</td><td>22.4</td><td>41</td><td>645</td><td>5</td></tr> <tr><td>◎</td><td>WUG 83</td><td>83</td><td>G82</td><td>CTG82</td><td>80</td><td>114.2</td><td>82.8</td><td>23.2</td><td>44</td><td>771</td><td>2</td></tr> <tr><td>◎</td><td>WUG 101-92</td><td>101</td><td>G92</td><td>CTG92</td><td>93</td><td>135.9</td><td>94.2</td><td>23.0</td><td>46</td><td>1048</td><td>2</td></tr> <tr><td>◎</td><td>WUG 101-104</td><td>101</td><td>G104</td><td>CTG104</td><td>99</td><td>135.9</td><td>106.9</td><td>23.0</td><td>46</td><td>1011</td><td>2</td></tr> </table> <p>注1. ※印の品番は、JIS C 8350に該当しない製品です。</p> <p>注2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WUG 76	76	G70	CTG70	69	107.6	70.1	22.4	41	645	5	◎	WUG 83	83	G82	CTG82	80	114.2	82.8	23.2	44	771	2	◎	WUG 101-92	101	G92	CTG92	93	135.9	94.2	23.0	46	1048	2	◎	WUG 101-104	101	G104	CTG104	99	135.9	106.9	23.0	46	1011	2	<table border="1"> <tr><td>◎</td><td>WUG 76</td><td>76</td><td>G70</td><td>CTG70</td><td>69</td><td>107.6</td><td>70.1</td><td>22.4</td><td>41</td><td>645</td><td>5</td></tr> <tr><td>◎</td><td>WUG 83</td><td>83</td><td>G82</td><td>CTG82</td><td>80</td><td>114.2</td><td>82.8</td><td>23.2</td><td>44</td><td>771</td><td>2</td></tr> <tr><td>◎</td><td>WUG 101-92</td><td>101</td><td>G92</td><td>CTG92</td><td>93</td><td>135.9</td><td>94.2</td><td>23.0</td><td>46</td><td>1048</td><td>2</td></tr> <tr><td>◎</td><td>WUG 101-104</td><td>101</td><td>G104</td><td>CTG104</td><td>99</td><td>135.9</td><td>106.9</td><td>23.0</td><td>46</td><td>1011</td><td>2</td></tr> </table> <p>注1. ※印の品番は、JIS C 8350に該当しない製品です。 注2. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WUG 76	76	G70	CTG70	69	107.6	70.1	22.4	41	645	5	◎	WUG 83	83	G82	CTG82	80	114.2	82.8	23.2	44	771	2	◎	WUG 101-92	101	G92	CTG92	93	135.9	94.2	23.0	46	1048	2	◎	WUG 101-104	101	G104	CTG104	99	135.9	106.9	23.0	46	1011	2
◎	WUG 76	76	G70	CTG70	69	107.6	70.1	22.4	41	645	5																																																																																							
◎	WUG 83	83	G82	CTG82	80	114.2	82.8	23.2	44	771	2																																																																																							
◎	WUG 101-92	101	G92	CTG92	93	135.9	94.2	23.0	46	1048	2																																																																																							
◎	WUG 101-104	101	G104	CTG104	99	135.9	106.9	23.0	46	1011	2																																																																																							
◎	WUG 76	76	G70	CTG70	69	107.6	70.1	22.4	41	645	5																																																																																							
◎	WUG 83	83	G82	CTG82	80	114.2	82.8	23.2	44	771	2																																																																																							
◎	WUG 101-92	101	G92	CTG92	93	135.9	94.2	23.0	46	1048	2																																																																																							
◎	WUG 101-104	101	G104	CTG104	99	135.9	106.9	23.0	46	1011	2																																																																																							
フリカチューブ 防水プリカ用附属品 防水コンビネーション カップリング WUC	<table border="1"> <tr><td>◎</td><td>WUC 50</td><td>38</td><td>C39</td><td>34</td><td>35.4</td><td>21.0</td><td>39</td><td>248</td><td>10</td></tr> <tr><td>◎</td><td>WUC 63</td><td>50</td><td>C51</td><td>CTC51</td><td>47</td><td>78.6</td><td>48.1</td><td>21.0</td><td>39</td><td>352</td><td>5</td></tr> <tr><td>◎</td><td>WUC 63</td><td>63</td><td>C63</td><td>CTC63</td><td>59</td><td>92.4</td><td>60.0</td><td>22.7</td><td>40</td><td>488</td><td>5</td></tr> <tr><td>◎</td><td>WUC 76</td><td>76</td><td>C75</td><td>CTC75</td><td>71</td><td>107.6</td><td>72.7</td><td>22.4</td><td>41</td><td>624</td><td>5</td></tr> </table> <p>追加</p> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WUC 50	38	C39	34	35.4	21.0	39	248	10	◎	WUC 63	50	C51	CTC51	47	78.6	48.1	21.0	39	352	5	◎	WUC 63	63	C63	CTC63	59	92.4	60.0	22.7	40	488	5	◎	WUC 76	76	C75	CTC75	71	107.6	72.7	22.4	41	624	5	<table border="1"> <tr><td>◎</td><td>WUC 50</td><td>38</td><td>C39</td><td>34</td><td>35.4</td><td>21.0</td><td>39</td><td>248</td><td>10</td></tr> <tr><td>◎</td><td>WUC 50</td><td>50</td><td>C51</td><td>CTC51</td><td>47</td><td>78.6</td><td>48.1</td><td>21.0</td><td>39</td><td>352</td><td>5</td></tr> <tr><td>◎</td><td>WUC 63</td><td>63</td><td>C63</td><td>CTC63</td><td>59</td><td>92.4</td><td>60.0</td><td>22.7</td><td>40</td><td>488</td><td>5</td></tr> <tr><td>◎</td><td>WUC 76</td><td>76</td><td>C75</td><td>CTC75</td><td>71</td><td>107.6</td><td>72.7</td><td>22.4</td><td>41</td><td>624</td><td>5</td></tr> </table> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WUC 50	38	C39	34	35.4	21.0	39	248	10	◎	WUC 50	50	C51	CTC51	47	78.6	48.1	21.0	39	352	5	◎	WUC 63	63	C63	CTC63	59	92.4	60.0	22.7	40	488	5	◎	WUC 76	76	C75	CTC75	71	107.6	72.7	22.4	41	624	5				
◎	WUC 50	38	C39	34	35.4	21.0	39	248	10																																																																																									
◎	WUC 63	50	C51	CTC51	47	78.6	48.1	21.0	39	352	5																																																																																							
◎	WUC 63	63	C63	CTC63	59	92.4	60.0	22.7	40	488	5																																																																																							
◎	WUC 76	76	C75	CTC75	71	107.6	72.7	22.4	41	624	5																																																																																							
◎	WUC 50	38	C39	34	35.4	21.0	39	248	10																																																																																									
◎	WUC 50	50	C51	CTC51	47	78.6	48.1	21.0	39	352	5																																																																																							
◎	WUC 63	63	C63	CTC63	59	92.4	60.0	22.7	40	488	5																																																																																							
◎	WUC 76	76	C75	CTC75	71	107.6	72.7	22.4	41	624	5																																																																																							
267	防水プリカ用附属品 防水コンビネーション カップリング WKI	<table border="1"> <tr><td>◎</td><td>WKI 76</td><td>76</td><td>G70</td><td>70</td><td>114.2</td><td>71.4</td><td>54.0</td><td>41</td><td>882</td><td>2</td></tr> <tr><td>◎</td><td>WKI 83</td><td>83</td><td>G82</td><td>80</td><td>114.2</td><td>82.1</td><td>57.8</td><td>44</td><td>1053</td><td>2</td></tr> <tr><td>◎</td><td>WKI 101-92</td><td>101</td><td>G92</td><td>94</td><td>135.9</td><td>95.7</td><td>63.6</td><td>46</td><td>1416</td><td>2</td></tr> <tr><td>◎</td><td>WKI 101-104</td><td>101</td><td>G104</td><td>99</td><td>135.9</td><td>100.8</td><td>64.4</td><td>46</td><td>1481</td><td>2</td></tr> </table> <p>追加</p> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WKI 76	76	G70	70	114.2	71.4	54.0	41	882	2	◎	WKI 83	83	G82	80	114.2	82.1	57.8	44	1053	2	◎	WKI 101-92	101	G92	94	135.9	95.7	63.6	46	1416	2	◎	WKI 101-104	101	G104	99	135.9	100.8	64.4	46	1481	2	<table border="1"> <tr><td>◎</td><td>WKI 76</td><td>76</td><td>G70</td><td>70</td><td>114.2</td><td>71.4</td><td>54.0</td><td>41</td><td>882</td><td>2</td></tr> <tr><td>◎</td><td>WKI 83</td><td>83</td><td>G82</td><td>80</td><td>114.2</td><td>82.1</td><td>57.8</td><td>44</td><td>1053</td><td>2</td></tr> <tr><td>◎</td><td>WKI 101-92</td><td>101</td><td>G92</td><td>94</td><td>135.9</td><td>95.7</td><td>63.6</td><td>46</td><td>1416</td><td>2</td></tr> <tr><td>◎</td><td>WKI 101-104</td><td>101</td><td>G104</td><td>99</td><td>135.9</td><td>100.8</td><td>64.4</td><td>46</td><td>1481</td><td>2</td></tr> </table> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	◎	WKI 76	76	G70	70	114.2	71.4	54.0	41	882	2	◎	WKI 83	83	G82	80	114.2	82.1	57.8	44	1053	2	◎	WKI 101-92	101	G92	94	135.9	95.7	63.6	46	1416	2	◎	WKI 101-104	101	G104	99	135.9	100.8	64.4	46	1481	2							
◎	WKI 76	76	G70	70	114.2	71.4	54.0	41	882	2																																																																																								
◎	WKI 83	83	G82	80	114.2	82.1	57.8	44	1053	2																																																																																								
◎	WKI 101-92	101	G92	94	135.9	95.7	63.6	46	1416	2																																																																																								
◎	WKI 101-104	101	G104	99	135.9	100.8	64.4	46	1481	2																																																																																								
◎	WKI 76	76	G70	70	114.2	71.4	54.0	41	882	2																																																																																								
◎	WKI 83	83	G82	80	114.2	82.1	57.8	44	1053	2																																																																																								
◎	WKI 101-92	101	G92	94	135.9	95.7	63.6	46	1416	2																																																																																								
◎	WKI 101-104	101	G104	99	135.9	100.8	64.4	46	1481	2																																																																																								

頁	商品名	修正内容	修正後																																																																		
267	<p>プリカチューブ</p> <p>防水プリカ用附属品 防水コンビネーション カップリング</p> <p>WKE</p>	<table border="1"> <tr> <td>○</td> <td>WKE 50</td> <td>50</td> <td>E51/C51</td> <td>47</td> <td>78.6</td> <td>48.3</td> <td>27.0</td> <td>39</td> <td>399</td> <td>5</td> </tr> <tr> <td>○</td> <td>WKE 63</td> <td>63</td> <td>E63/C63</td> <td>60</td> <td>92.4</td> <td>61.2</td> <td>35.0</td> <td>40</td> <td>515</td> <td>2</td> </tr> <tr> <td>○</td> <td>WKE 76</td> <td>76</td> <td>E75/C75</td> <td>72</td> <td>107.6</td> <td>73.9</td> <td>35.0</td> <td>41</td> <td>693</td> <td>2</td> </tr> </table> <p>注1.ねじなし電線管(E管)を接続の場合は電気用品安全法(PSE)適合品です。 注2.薄鋼電線管(C管)を接続の場合は電気用品安全法(PSE)適用外です。</p> <p>追加</p> <p>注3.接続できるプリカチューブの詳細サイズについては、 プリカチューブの各頁をご参照下さい。</p>	○	WKE 50	50	E51/C51	47	78.6	48.3	27.0	39	399	5	○	WKE 63	63	E63/C63	60	92.4	61.2	35.0	40	515	2	○	WKE 76	76	E75/C75	72	107.6	73.9	35.0	41	693	2	<table border="1"> <tr> <td>○</td> <td>WKE 50</td> <td>50</td> <td>E51/C51</td> <td>47</td> <td>78.6</td> <td>48.3</td> <td>27.0</td> <td>39</td> <td>399</td> <td>5</td> </tr> <tr> <td>○</td> <td>WKE 63</td> <td>63</td> <td>E63/C63</td> <td>60</td> <td>92.4</td> <td>61.2</td> <td>35.0</td> <td>40</td> <td>515</td> <td>2</td> </tr> <tr> <td>○</td> <td>WKE 76</td> <td>76</td> <td>E75/C75</td> <td>72</td> <td>107.6</td> <td>73.9</td> <td>35.0</td> <td>41</td> <td>693</td> <td>2</td> </tr> </table> <p>注1.ねじなし電線管(E管)を接続の場合は電気用品安全法(PSE)適合品です。 注2.薄鋼電線管(C管)を接続の場合は電気用品安全法(PSE)適用外です。 注3.接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○	WKE 50	50	E51/C51	47	78.6	48.3	27.0	39	399	5	○	WKE 63	63	E63/C63	60	92.4	61.2	35.0	40	515	2	○	WKE 76	76	E75/C75	72	107.6	73.9	35.0	41	693	2
○	WKE 50	50	E51/C51	47	78.6	48.3	27.0	39	399	5																																																											
○	WKE 63	63	E63/C63	60	92.4	61.2	35.0	40	515	2																																																											
○	WKE 76	76	E75/C75	72	107.6	73.9	35.0	41	693	2																																																											
○	WKE 50	50	E51/C51	47	78.6	48.3	27.0	39	399	5																																																											
○	WKE 63	63	E63/C63	60	92.4	61.2	35.0	40	515	2																																																											
○	WKE 76	76	E75/C75	72	107.6	73.9	35.0	41	693	2																																																											
268	<p>プリカチューブ</p> <p>防水プリカ用附属品 PLP用 コンビネーション カップリング</p> <p>WKJ</p>	<table border="1"> <tr> <td>○</td> <td>WKJ 63</td> <td>PEC</td> <td>63</td> </tr> <tr> <td>○</td> <td>WKJ 76</td> <td></td> <td>76</td> </tr> <tr> <td>○</td> <td>WKJ 83</td> <td></td> <td>83</td> </tr> <tr> <td>○</td> <td>WKJ 101-92</td> <td></td> <td>101</td> </tr> <tr> <td>○</td> <td>WKJ 101-104</td> <td></td> <td>101</td> </tr> </table> <p>追加</p> <p>注. 接続できるプリカチューブの詳細サイズについては、 プリカチューブの各頁をご参照下さい。</p>	○	WKJ 63	PEC	63	○	WKJ 76		76	○	WKJ 83		83	○	WKJ 101-92		101	○	WKJ 101-104		101	<table border="1"> <tr> <td>○</td> <td>WKJ 63</td> <td>PEC</td> <td>63</td> </tr> <tr> <td>○</td> <td>WKJ 76</td> <td></td> <td>76</td> </tr> <tr> <td>○</td> <td>WKJ 83</td> <td></td> <td>83</td> </tr> <tr> <td>○</td> <td>WKJ 101-92</td> <td></td> <td>101</td> </tr> <tr> <td>○</td> <td>WKJ 101-104</td> <td></td> <td>101</td> </tr> </table> <p>注. 接続できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○	WKJ 63	PEC	63	○	WKJ 76		76	○	WKJ 83		83	○	WKJ 101-92		101	○	WKJ 101-104		101																										
○	WKJ 63	PEC	63																																																																		
○	WKJ 76		76																																																																		
○	WKJ 83		83																																																																		
○	WKJ 101-92		101																																																																		
○	WKJ 101-104		101																																																																		
○	WKJ 63	PEC	63																																																																		
○	WKJ 76		76																																																																		
○	WKJ 83		83																																																																		
○	WKJ 101-92		101																																																																		
○	WKJ 101-104		101																																																																		
269	<p>プリカチューブ</p> <p>防水プリカ用附属品 ステンレス製 万能サドル</p> <p>LS2AV (1本止め)</p>	<table border="1"> <tr> <td>○</td> <td>LS2AV 71</td> <td>63</td> <td>6.5</td> <td>117</td> <td>6.5</td> <td>20</td> </tr> <tr> <td>○</td> <td>LS2AV 84</td> <td>76</td> <td>6.5</td> <td>131</td> <td>113</td> <td>30</td> </tr> <tr> <td>○</td> <td>LS2AV 92</td> <td>83</td> <td>6.5</td> <td>138</td> <td>120</td> <td>30</td> </tr> <tr> <td>○</td> <td>LS2AV 111</td> <td>101</td> <td>6.5</td> <td>157</td> <td>139</td> <td>30</td> </tr> </table> <p>追加</p> <p>注. 取付できるプリカチューブの詳細サイズについては、 プリカチューブの各頁をご参照下さい。</p>	○	LS2AV 71	63	6.5	117	6.5	20	○	LS2AV 84	76	6.5	131	113	30	○	LS2AV 92	83	6.5	138	120	30	○	LS2AV 111	101	6.5	157	139	30	<table border="1"> <tr> <td>○</td> <td>LS2AV 71</td> <td>63</td> <td>6.5</td> <td>117</td> <td>6.5</td> <td>20</td> </tr> <tr> <td>○</td> <td>LS2AV 84</td> <td>76</td> <td>6.5</td> <td>131</td> <td>113</td> <td>30</td> </tr> <tr> <td>○</td> <td>LS2AV 92</td> <td>83</td> <td>6.5</td> <td>138</td> <td>120</td> <td>30</td> </tr> <tr> <td>○</td> <td>LS2AV 111</td> <td>101</td> <td>6.5</td> <td>157</td> <td>139</td> <td>30</td> </tr> </table> <p>注. 取付できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○	LS2AV 71	63	6.5	117	6.5	20	○	LS2AV 84	76	6.5	131	113	30	○	LS2AV 92	83	6.5	138	120	30	○	LS2AV 111	101	6.5	157	139	30										
○	LS2AV 71	63	6.5	117	6.5	20																																																															
○	LS2AV 84	76	6.5	131	113	30																																																															
○	LS2AV 92	83	6.5	138	120	30																																																															
○	LS2AV 111	101	6.5	157	139	30																																																															
○	LS2AV 71	63	6.5	117	6.5	20																																																															
○	LS2AV 84	76	6.5	131	113	30																																																															
○	LS2AV 92	83	6.5	138	120	30																																																															
○	LS2AV 111	101	6.5	157	139	30																																																															
	<p>プリカチューブ</p> <p>防水プリカ用附属品 ステンレス製 万能サドル</p> <p>LS2AV (2本止め)</p>	<table border="1"> <tr> <td>○</td> <td>LS2AV 28</td> <td>PE</td> <td>15</td> <td>5.5</td> <td>76</td> <td>62</td> <td>20</td> </tr> <tr> <td>○</td> <td>LS2AV 31</td> <td>PEC</td> <td>17</td> <td>5.5</td> <td>81</td> <td>67</td> <td>20</td> </tr> <tr> <td>○</td> <td>LS2AV 42</td> <td></td> <td>24</td> <td>5.5</td> <td>95</td> <td>81</td> <td>20</td> </tr> </table> <p>追加</p> <p>注. 取付できるプリカチューブの詳細サイズについては、 プリカチューブの各頁をご参照下さい。</p>	○	LS2AV 28	PE	15	5.5	76	62	20	○	LS2AV 31	PEC	17	5.5	81	67	20	○	LS2AV 42		24	5.5	95	81	20	<table border="1"> <tr> <td>○</td> <td>LS2AV 28</td> <td>PE</td> <td>15</td> <td>5.5</td> <td>76</td> <td>62</td> <td>20</td> </tr> <tr> <td>○</td> <td>LS2AV 31</td> <td>PEC</td> <td>17</td> <td>5.5</td> <td>81</td> <td>67</td> <td>20</td> </tr> <tr> <td>○</td> <td>LS2AV 42</td> <td></td> <td>24</td> <td>5.5</td> <td>95</td> <td>81</td> <td>20</td> </tr> </table> <p>注. 取付できるプリカチューブの詳細サイズについては、プリカチューブの各頁をご参照下さい。</p>	○	LS2AV 28	PE	15	5.5	76	62	20	○	LS2AV 31	PEC	17	5.5	81	67	20	○	LS2AV 42		24	5.5	95	81	20																		
○	LS2AV 28	PE	15	5.5	76	62	20																																																														
○	LS2AV 31	PEC	17	5.5	81	67	20																																																														
○	LS2AV 42		24	5.5	95	81	20																																																														
○	LS2AV 28	PE	15	5.5	76	62	20																																																														
○	LS2AV 31	PEC	17	5.5	81	67	20																																																														
○	LS2AV 42		24	5.5	95	81	20																																																														