

頁	商品名	修正内容	修正後																																																																																																																		
130	サンフレキROBO N型附属品 コネクタ ノックアウト接続用 NBG (標準品)	<table border="1"> <tr><td>○</td><td>NBG 20</td><td>NF 20</td><td>14</td><td>34.2</td><td>38.6</td><td>44.0</td><td>15.2</td><td>14.0</td><td>19</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 32</td><td>NF 32</td><td>25</td><td>50.0</td><td>47.9</td><td>43.6</td><td>26.0</td><td>15.0</td><td>24</td><td>9.0</td></tr> <tr><td>○</td><td>NBG 40</td><td>NFX 40</td><td>32</td><td>59.5</td><td>60.2</td><td>54.6</td><td>33.3</td><td>16.0</td><td>28</td><td>10.0</td></tr> <tr><td>○</td><td>NBG 50</td><td></td><td>50</td><td>39</td><td>70.3</td><td>68.4</td><td>62.7</td><td>39.9</td><td>16.0</td><td>32</td><td>10.0</td></tr> <tr><td>○</td><td>NBG 63</td><td></td><td>63</td><td>51</td><td>84.4</td><td>79.0</td><td>78.6</td><td>51.7</td><td>18.0</td><td>36</td><td>11.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>追加</p> <p>注 2. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	NBG 20	NF 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8	○	NBG 32	NF 32	25	50.0	47.9	43.6	26.0	15.0	24	9.0	○	NBG 40	NFX 40	32	59.5	60.2	54.6	33.3	16.0	28	10.0	○	NBG 50		50	39	70.3	68.4	62.7	39.9	16.0	32	10.0	○	NBG 63		63	51	84.4	79.0	78.6	51.7	18.0	36	11.0	<table border="1"> <tr><td>○</td><td>NBG 20</td><td>NF 20</td><td>14</td><td>34.2</td><td>38.6</td><td>44.0</td><td>15.2</td><td>14.0</td><td>19</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 32</td><td>NF 32</td><td>25</td><td>50.0</td><td>47.9</td><td>43.6</td><td>26.0</td><td>15.0</td><td>24</td><td>9.0</td></tr> <tr><td>○</td><td>NBG 40</td><td>NFX 40</td><td>32</td><td>59.5</td><td>60.2</td><td>54.6</td><td>33.3</td><td>16.0</td><td>28</td><td>10.0</td></tr> <tr><td>○</td><td>NBG 50</td><td></td><td>50</td><td>39</td><td>70.3</td><td>68.4</td><td>62.7</td><td>39.9</td><td>16.0</td><td>32</td><td>10.0</td></tr> <tr><td>○</td><td>NBG 63</td><td></td><td>63</td><td>51</td><td>84.4</td><td>79.0</td><td>78.6</td><td>51.7</td><td>18.0</td><td>36</td><td>11.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>注 2. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	NBG 20	NF 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8	○	NBG 32	NF 32	25	50.0	47.9	43.6	26.0	15.0	24	9.0	○	NBG 40	NFX 40	32	59.5	60.2	54.6	33.3	16.0	28	10.0	○	NBG 50		50	39	70.3	68.4	62.7	39.9	16.0	32	10.0	○	NBG 63		63	51	84.4	79.0	78.6	51.7	18.0	36	11.0
	○	NBG 20	NF 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8																																																																																																										
	○	NBG 32	NF 32	25	50.0	47.9	43.6	26.0	15.0	24	9.0																																																																																																										
○	NBG 40	NFX 40	32	59.5	60.2	54.6	33.3	16.0	28	10.0																																																																																																											
○	NBG 50		50	39	70.3	68.4	62.7	39.9	16.0	32	10.0																																																																																																										
○	NBG 63		63	51	84.4	79.0	78.6	51.7	18.0	36	11.0																																																																																																										
○	NBG 20	NF 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8																																																																																																											
○	NBG 32	NF 32	25	50.0	47.9	43.6	26.0	15.0	24	9.0																																																																																																											
○	NBG 40	NFX 40	32	59.5	60.2	54.6	33.3	16.0	28	10.0																																																																																																											
○	NBG 50		50	39	70.3	68.4	62.7	39.9	16.0	32	10.0																																																																																																										
○	NBG 63		63	51	84.4	79.0	78.6	51.7	18.0	36	11.0																																																																																																										
サンフレキROBO N型附属品 コネクタ ノックアウト接続用 NBG (経違い品)	<table border="1"> <tr><td>○</td><td>NBG 20 22</td><td>NP 20</td><td>14</td><td>34.2</td><td>38.6</td><td>44.0</td><td>15.2</td><td>14.0</td><td>19</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 20 28</td><td>NF 20</td><td>14</td><td>34.2</td><td>47.9</td><td>29.0</td><td>15.2</td><td>15.0</td><td>19</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 25 16</td><td>NFX 25</td><td>13</td><td>41.5</td><td>38.6</td><td>38.6</td><td>14.4</td><td>13.0</td><td>21</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 25 28</td><td></td><td>19</td><td>41.5</td><td>47.9</td><td>44.0</td><td>20.0</td><td>15.0</td><td>21</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 40 54</td><td></td><td>40</td><td>33</td><td>59.5</td><td>79.0</td><td>74.0</td><td>34.0</td><td>18.0</td><td>28</td><td>5.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>追加</p> <p>注 5. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	NBG 20 22	NP 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8	○	NBG 20 28	NF 20	14	34.2	47.9	29.0	15.2	15.0	19	4.5	○	NBG 25 16	NFX 25	13	41.5	38.6	38.6	14.4	13.0	21	3.8	○	NBG 25 28		19	41.5	47.9	44.0	20.0	15.0	21	4.5	○	NBG 40 54		40	33	59.5	79.0	74.0	34.0	18.0	28	5.0	<table border="1"> <tr><td>○</td><td>NBG 20 22</td><td>NP 20</td><td>14</td><td>34.2</td><td>38.6</td><td>44.0</td><td>15.2</td><td>14.0</td><td>19</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 20 28</td><td>NF 20</td><td>14</td><td>34.2</td><td>47.9</td><td>29.0</td><td>15.2</td><td>15.0</td><td>19</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 25 16</td><td>NFX 25</td><td>13</td><td>41.5</td><td>38.6</td><td>38.6</td><td>14.4</td><td>13.0</td><td>21</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 25 28</td><td></td><td>19</td><td>41.5</td><td>47.9</td><td>44.0</td><td>20.0</td><td>15.0</td><td>21</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 40 54</td><td></td><td>40</td><td>33</td><td>59.5</td><td>79.0</td><td>74.0</td><td>34.0</td><td>18.0</td><td>28</td><td>5.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>注 2. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	NBG 20 22	NP 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8	○	NBG 20 28	NF 20	14	34.2	47.9	29.0	15.2	15.0	19	4.5	○	NBG 25 16	NFX 25	13	41.5	38.6	38.6	14.4	13.0	21	3.8	○	NBG 25 28		19	41.5	47.9	44.0	20.0	15.0	21	4.5	○	NBG 40 54		40	33	59.5	79.0	74.0	34.0	18.0	28	5.0			
○	NBG 20 22	NP 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8																																																																																																											
○	NBG 20 28	NF 20	14	34.2	47.9	29.0	15.2	15.0	19	4.5																																																																																																											
○	NBG 25 16	NFX 25	13	41.5	38.6	38.6	14.4	13.0	21	3.8																																																																																																											
○	NBG 25 28		19	41.5	47.9	44.0	20.0	15.0	21	4.5																																																																																																											
○	NBG 40 54		40	33	59.5	79.0	74.0	34.0	18.0	28	5.0																																																																																																										
○	NBG 20 22	NP 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8																																																																																																											
○	NBG 20 28	NF 20	14	34.2	47.9	29.0	15.2	15.0	19	4.5																																																																																																											
○	NBG 25 16	NFX 25	13	41.5	38.6	38.6	14.4	13.0	21	3.8																																																																																																											
○	NBG 25 28		19	41.5	47.9	44.0	20.0	15.0	21	4.5																																																																																																											
○	NBG 40 54		40	33	59.5	79.0	74.0	34.0	18.0	28	5.0																																																																																																										
サンフレキROBO N型附属品 コネクタ ノックアウト接続用 NBG※L※ (長いおねじ品)	<table border="1"> <tr><td>○</td><td>NBG 20 L21</td><td>NS 20</td><td>14</td><td>34.2</td><td>38.6</td><td>44.0</td><td>15.2</td><td>14.0</td><td>19</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 25 L21</td><td>NP 25</td><td>19</td><td>41.5</td><td>38.6</td><td>36.0</td><td>20.2</td><td>21.0</td><td>21</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 32 L24</td><td>NF 32</td><td>25</td><td>50.0</td><td>47.9</td><td>44.0</td><td>26.3</td><td>24.0</td><td>24</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 40 L24</td><td>NFX 40</td><td>33</td><td>59.5</td><td>60.2</td><td>53.0</td><td>33.7</td><td>24.0</td><td>28</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 50 L24</td><td></td><td>50</td><td>39</td><td>70.3</td><td>68.4</td><td>61.0</td><td>40.3</td><td>24.0</td><td>32</td><td>5.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>追加</p> <p>注 1. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	NBG 20 L21	NS 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8	○	NBG 25 L21	NP 25	19	41.5	38.6	36.0	20.2	21.0	21	3.8	○	NBG 32 L24	NF 32	25	50.0	47.9	44.0	26.3	24.0	24	4.5	○	NBG 40 L24	NFX 40	33	59.5	60.2	53.0	33.7	24.0	28	4.5	○	NBG 50 L24		50	39	70.3	68.4	61.0	40.3	24.0	32	5.0	<table border="1"> <tr><td>○</td><td>NBG 20 L21</td><td>NS 20</td><td>14</td><td>34.2</td><td>38.6</td><td>44.0</td><td>15.2</td><td>14.0</td><td>19</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 25 L21</td><td>NP 25</td><td>19</td><td>41.5</td><td>38.6</td><td>36.0</td><td>20.2</td><td>21.0</td><td>21</td><td>3.8</td></tr> <tr><td>○</td><td>NBG 32 L24</td><td>NF 32</td><td>25</td><td>50.0</td><td>47.9</td><td>44.0</td><td>26.3</td><td>24.0</td><td>24</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 40 L24</td><td>NFX 40</td><td>33</td><td>59.5</td><td>60.2</td><td>53.0</td><td>33.7</td><td>24.0</td><td>28</td><td>4.5</td></tr> <tr><td>○</td><td>NBG 50 L24</td><td></td><td>50</td><td>39</td><td>70.3</td><td>68.4</td><td>61.0</td><td>40.3</td><td>24.0</td><td>32</td><td>5.0</td></tr> </table> <p>注 1. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	NBG 20 L21	NS 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8	○	NBG 25 L21	NP 25	19	41.5	38.6	36.0	20.2	21.0	21	3.8	○	NBG 32 L24	NF 32	25	50.0	47.9	44.0	26.3	24.0	24	4.5	○	NBG 40 L24	NFX 40	33	59.5	60.2	53.0	33.7	24.0	28	4.5	○	NBG 50 L24		50	39	70.3	68.4	61.0	40.3	24.0	32	5.0			
○	NBG 20 L21	NS 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8																																																																																																											
○	NBG 25 L21	NP 25	19	41.5	38.6	36.0	20.2	21.0	21	3.8																																																																																																											
○	NBG 32 L24	NF 32	25	50.0	47.9	44.0	26.3	24.0	24	4.5																																																																																																											
○	NBG 40 L24	NFX 40	33	59.5	60.2	53.0	33.7	24.0	28	4.5																																																																																																											
○	NBG 50 L24		50	39	70.3	68.4	61.0	40.3	24.0	32	5.0																																																																																																										
○	NBG 20 L21	NS 20	14	34.2	38.6	44.0	15.2	14.0	19	3.8																																																																																																											
○	NBG 25 L21	NP 25	19	41.5	38.6	36.0	20.2	21.0	21	3.8																																																																																																											
○	NBG 32 L24	NF 32	25	50.0	47.9	44.0	26.3	24.0	24	4.5																																																																																																											
○	NBG 40 L24	NFX 40	33	59.5	60.2	53.0	33.7	24.0	28	4.5																																																																																																											
○	NBG 50 L24		50	39	70.3	68.4	61.0	40.3	24.0	32	5.0																																																																																																										
131	サンフレキROBO N型附属品 90°形コネクタ ノックアウト接続用 N90BG	<table border="1"> <tr><td>○</td><td>N90BG 32</td><td>NF 32</td><td>25</td><td>50.0</td><td>45.5</td><td>43.6</td><td>26.0</td><td>31</td><td>46</td><td>15.0</td><td>9.0</td></tr> <tr><td>○</td><td>N90BG 40</td><td>NFX 40</td><td>33</td><td>59.5</td><td>56.0</td><td>54.6</td><td>34.0</td><td>36</td><td>54</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N90BG 50</td><td></td><td>50</td><td>39</td><td>70.3</td><td>64.0</td><td>62.7</td><td>40.0</td><td>42</td><td>63</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N90BG 63</td><td></td><td>63</td><td>51</td><td>84.4</td><td>74.8</td><td>78.6</td><td>51.9</td><td>49</td><td>74</td><td>18.0</td><td>11.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>注 2. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部を通線する場合がありますので、最大外径の 40 ~ 60% の外径を目安として下さい。</p> <p>追加</p> <p>注 3. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	N90BG 32	NF 32	25	50.0	45.5	43.6	26.0	31	46	15.0	9.0	○	N90BG 40	NFX 40	33	59.5	56.0	54.6	34.0	36	54	16.0	10.0	○	N90BG 50		50	39	70.3	64.0	62.7	40.0	42	63	16.0	10.0	○	N90BG 63		63	51	84.4	74.8	78.6	51.9	49	74	18.0	11.0	<table border="1"> <tr><td>○</td><td>N90BG 32</td><td>NF 32</td><td>25</td><td>50.0</td><td>45.5</td><td>43.6</td><td>26.0</td><td>31</td><td>46</td><td>15.0</td><td>9.0</td></tr> <tr><td>○</td><td>N90BG 40</td><td>NFX 40</td><td>33</td><td>59.5</td><td>56.0</td><td>54.6</td><td>34.0</td><td>36</td><td>54</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N90BG 50</td><td></td><td>50</td><td>39</td><td>70.3</td><td>64.0</td><td>62.7</td><td>40.0</td><td>42</td><td>63</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N90BG 63</td><td></td><td>63</td><td>51</td><td>84.4</td><td>74.8</td><td>78.6</td><td>51.9</td><td>49</td><td>74</td><td>18.0</td><td>11.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>注 2. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。90°型本体部を通線する場合がありますので、最大外径の 40 ~ 60% の外径を目安として下さい。</p> <p>注 3. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	N90BG 32	NF 32	25	50.0	45.5	43.6	26.0	31	46	15.0	9.0	○	N90BG 40	NFX 40	33	59.5	56.0	54.6	34.0	36	54	16.0	10.0	○	N90BG 50		50	39	70.3	64.0	62.7	40.0	42	63	16.0	10.0	○	N90BG 63		63	51	84.4	74.8	78.6	51.9	49	74	18.0	11.0														
	○	N90BG 32	NF 32	25	50.0	45.5	43.6	26.0	31	46	15.0	9.0																																																																																																									
○	N90BG 40	NFX 40	33	59.5	56.0	54.6	34.0	36	54	16.0	10.0																																																																																																										
○	N90BG 50		50	39	70.3	64.0	62.7	40.0	42	63	16.0	10.0																																																																																																									
○	N90BG 63		63	51	84.4	74.8	78.6	51.9	49	74	18.0	11.0																																																																																																									
○	N90BG 32	NF 32	25	50.0	45.5	43.6	26.0	31	46	15.0	9.0																																																																																																										
○	N90BG 40	NFX 40	33	59.5	56.0	54.6	34.0	36	54	16.0	10.0																																																																																																										
○	N90BG 50		50	39	70.3	64.0	62.7	40.0	42	63	16.0	10.0																																																																																																									
○	N90BG 63		63	51	84.4	74.8	78.6	51.9	49	74	18.0	11.0																																																																																																									
サンフレキROBO N型附属品 45°形コネクタ ノックアウト接続用 N45BG	<table border="1"> <tr><td>○</td><td>N45BG 32</td><td>NF 32</td><td>25</td><td>50.0</td><td>45.5</td><td>43.6</td><td>26.0</td><td>16</td><td>31</td><td>15.0</td><td>9.0</td></tr> <tr><td>○</td><td>N45BG 40</td><td>NFX 40</td><td>33</td><td>59.5</td><td>56.0</td><td>54.6</td><td>34.0</td><td>19</td><td>38</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N45BG 50</td><td></td><td>50</td><td>39</td><td>70.3</td><td>64.0</td><td>62.7</td><td>39.9</td><td>21</td><td>42</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N45BG 63</td><td></td><td>63</td><td>51</td><td>84.4</td><td>74.8</td><td>78.6</td><td>51.8</td><td>24</td><td>49</td><td>18.0</td><td>11.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>注 2. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。45°型本体部を通線する場合がありますので、最大外径の 40 ~ 60% の外径を目安として下さい。</p> <p>追加</p> <p>注 3. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	N45BG 32	NF 32	25	50.0	45.5	43.6	26.0	16	31	15.0	9.0	○	N45BG 40	NFX 40	33	59.5	56.0	54.6	34.0	19	38	16.0	10.0	○	N45BG 50		50	39	70.3	64.0	62.7	39.9	21	42	16.0	10.0	○	N45BG 63		63	51	84.4	74.8	78.6	51.8	24	49	18.0	11.0	<table border="1"> <tr><td>○</td><td>N45BG 32</td><td>NF 32</td><td>25</td><td>50.0</td><td>45.5</td><td>43.6</td><td>26.0</td><td>16</td><td>31</td><td>15.0</td><td>9.0</td></tr> <tr><td>○</td><td>N45BG 40</td><td>NFX 40</td><td>33</td><td>59.5</td><td>56.0</td><td>54.6</td><td>34.0</td><td>19</td><td>38</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N45BG 50</td><td></td><td>50</td><td>39</td><td>70.3</td><td>64.0</td><td>62.7</td><td>39.9</td><td>21</td><td>42</td><td>16.0</td><td>10.0</td></tr> <tr><td>○</td><td>N45BG 63</td><td></td><td>63</td><td>51</td><td>84.4</td><td>74.8</td><td>78.6</td><td>51.8</td><td>24</td><td>49</td><td>18.0</td><td>11.0</td></tr> </table> <p>注 1. UL 認定品ではありません。</p> <p>注 2. ※印について、挿入できるケーブル最大外径は本体最小内径をもとにしています。45°型本体部を通線する場合がありますので、最大外径の 40 ~ 60% の外径を目安として下さい。</p> <p>注 3. 接続できるサンフレキ ROBO の詳細サイズについては、サンフレキ ROBO の各頁をご参照下さい。</p>	○	N45BG 32	NF 32	25	50.0	45.5	43.6	26.0	16	31	15.0	9.0	○	N45BG 40	NFX 40	33	59.5	56.0	54.6	34.0	19	38	16.0	10.0	○	N45BG 50		50	39	70.3	64.0	62.7	39.9	21	42	16.0	10.0	○	N45BG 63		63	51	84.4	74.8	78.6	51.8	24	49	18.0	11.0															
○	N45BG 32	NF 32	25	50.0	45.5	43.6	26.0	16	31	15.0	9.0																																																																																																										
○	N45BG 40	NFX 40	33	59.5	56.0	54.6	34.0	19	38	16.0	10.0																																																																																																										
○	N45BG 50		50	39	70.3	64.0	62.7	39.9	21	42	16.0	10.0																																																																																																									
○	N45BG 63		63	51	84.4	74.8	78.6	51.8	24	49	18.0	11.0																																																																																																									
○	N45BG 32	NF 32	25	50.0	45.5	43.6	26.0	16	31	15.0	9.0																																																																																																										
○	N45BG 40	NFX 40	33	59.5	56.0	54.6	34.0	19	38	16.0	10.0																																																																																																										
○	N45BG 50		50	39	70.3	64.0	62.7	39.9	21	42	16.0	10.0																																																																																																									
○	N45BG 63		63	51	84.4	74.8	78.6	51.8	24	49	18.0	11.0																																																																																																									